

Overview of items

Family number	Extension Partial (T) Full (V) Over (Ü)	Max. WLL per pair in kg	Slide length in mm (retracted)	Material Steel (S) Stainless steel (ES) Aluminium (A)	Horizontal mounting	Mounting bracket (21335-80)	Soft- Close	Push to open	Auto- retrac- tion	Latch open	Latch closed	Quick frontal release
21334	V	20	150 - 500	S								
21334-05	T	35	305 - 711	S						X		
21334-10	V	45	150 - 550	S								
21334-15	V	50	199 - 700	S		X	X	X	X	X	X	X
21334-20	T	50	305 - 711	S	X							
21334-25	T	50	300 - 700	S	X					X	X	
21334-30	T	50	250 - 700	S		X				X	X	X
21334-35	Ü	55	350 - 700	S		X					X	
21334-40	Ü	60	300 - 700	S							X	X
21334-45	T	65	305 - 711	S	X					X		X
21334-50	T	65	300 - 700	ES	X						X	
21334-55	Ü	68	305 - 711	S	X					X		X
21334-60	Ü	68	305 - 711	S	X						X	X
21334-65	Ü	68	305 - 711	S	X						X	
21334-70	Ü	70	305 - 711	S	X							
21334-75	Ü	70	305 - 711	S	X					X		X
21334-80	Ü	70	305 - 711	ES	X					X		X

Overview of items

Family number	Extension Partial (T) Full (V) Over (Ü)	Max. WLL per pair in kg	Slide length in mm (retracted)	Material Steel (S) Stainless steel (ES) Aluminium (A)	Horizontal mounting	Mounting bracket (21335-80)	Soft- Close	Push to open	Auto- retrac- tion	Latch open	Latch closed	Quick frontal release
21334-85	V	80	300 - 700	ES	X						X	
21334-90	Ü	82	406 - 762	S	X					X		X
21334-95	Ü	90	305 - 660	ES	X					X		X
21335	V	100	400 - 700	S	X		X				X	
21335-05	Ü	100	300 - 700	S			X				X	
21335-10	V	124	305 - 711	S								X
21335-15	V	160	305 - 914	S	X						X	X
21335-20	Ü	160	300 - 1100	S							X	
21335-25	V	227	305 - 1524	S						X	X	
21335-30	V	272	254 - 1524	S	X							
21335-35	V	300	300 - 1000	A								